Jaep

Wet abrasi

This instrument is user to abrasion, scrub and wise performance of many materia as perform the abrasion scru wet and dry condition, in a re controlled condition everyday use or wea detergent performance determined. It is widely water-based coating field,

suitable for testing paints. coatings, leather, wood, plastic, printing materials, fibre, etc.

Various brushes, pads, sponges and crockmeter attachment available according to the various ISO, DIN and ASTM standards

Features

- Two models: 2 or 4 teststations
- Large lcd with touch-screen operation
- Test fluid flow controlled by a peristaltic pump

Technical details

Abrasion Sample Mains

Scrub rate

37 ± 1 /min (2 station) 1-65 /min (4 station) 0-9999 cycles ≤ 25 mm thickness 220 V/50 Hz

Standards

ester

ISO 11998 • EN 13300 • DIN 53778 • BS 3900 • ASTM D2486 • ASTM D3450 • ASTM F1319 • ISO 105-X12 • PSA D45 1010

C +31 36 26 000 16

⊠ info@jarp.nl